



HHA081Z

Moulded Case Circuit Breaker h3 x160 TM FIX 4P4D 80A 25kA CTC

Technical characteristics

Architecture

Number of poles 4 P

Main electrical features

Rated operational voltage Ue 220 / 415 V

Frequency 50/60 Hz

Voltage

Rated insulation voltage 690 V

Rated impulse withstand voltage 8 kV

Electric current

Rated service breaking capacity Ics under 400V AC according IEC 60947-2 20 kA

Dimensions

Depth of installed product 68 mm

Height of installed product 130 mm

Width of installed product 100 mm

Power

Total power loss under IN 18.9 W

Endurance

Electric endurance in number of cycles 1000

Number of mechanical operations 4000

Equipment

Number of auxiliary contacts as normally closed contact 0

Number of auxiliary contacts as normally open contact 0

Number of auxiliary contacts as change-over contact 0

Can be accessorized Yes

Standards

Standard text IEC 60947-2

European directive WEEE concerned