



HHA125Z

## Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 125A 25kA CTC

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of poles	3 P

#### Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV

#### Electric current

Rated service breaking capacity Ics under 400V AC according IEC 60947-2	20 kA
---	-------

#### Dimensions

Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	75 mm

#### Power

Total power loss under IN	33 W
---------------------------	------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

#### Connection

Type of connection	with screw
--------------------	------------

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes

#### Standards

Standard text	IEC 60947-2
---------------	-------------