



HHA126U

**Moulded Case Circuit Breaker h3 x160 TM ADJ 4P4D N0-100% 125A 25kA CTC**

**Technical characteristics**

**Architecture**

Number of poles	4 P
-----------------	-----

**Main electrical features**

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV

**Electric current**

Rated service breaking capacity Ics under 400V AC according IEC 60947-2	20 kA
---	-------

**Dimensions**

Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	100 mm

**Power**

Total power loss under IN	33 W
---------------------------	------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Connection**

Type of connection	with screw
--------------------	------------

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes

**Standards**

European directive WEEE	concerned
-------------------------	-----------