



HHB200Z

**Moulded Case Circuit Breaker X250 3P 25kA 200A TM**

**Technical characteristics**

**Architecture**

Number of poles	3 P
-----------------	-----

**Main electrical features**

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

**Power**

Total power loss under IN	38.4 W
---------------------------	--------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Connection**

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Type of connection	Terminal

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP4X
---------------------	------

**Use conditions**

Operating temperature	-25...70 °C
-----------------------	-------------