



HIM402

Modular change-over switch 4x20A

Technical characteristics

Architecture

Number of poles	4 P
Type of pole	4 P

Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

Power

Total power loss under IN	1.6 W
---------------------------	-------

Endurance

Number of mechanical operations	10000
---------------------------------	-------

Cover, door

Interlockable	Yes
---------------	-----

Connection

Connection cross-sect. flexible conductor	1,5 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 16mm ²
Type of connection	with screw

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

Standards

Standard text	IEC 60947-3
---------------	-------------

Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------