



HIM404

## Modular change-over switch 4x40A

### Technical characteristics

#### Architecture

Number of poles	4 P
Type of pole	4 P

#### Main electrical features

Rated operational voltage U <sub>e</sub>	380 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

#### Power

Total power loss under I <sub>N</sub>	3.6 W
---------------------------------------	-------

#### Endurance

Number of mechanical operations	10000
---------------------------------	-------

#### Cover, door

Interlockable	Yes
---------------	-----

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

#### Standards

Standard text	IEC 60947-3
European directive WEEE	concerned

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------