



HIM404

Modular change-over switch 4x40A

Technical Characteristics

Number of poles	4 P
Type of pole	4 P
Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz
Rated current	40 A
Total power loss under IN	3.6 W
Interlockable	Yes
Type of connection	with screw
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	No
Standard text	IEC 60947-3
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-20...70 °C