



HMF290T

**MCB 2P 10kA C-100A 3M**

**Technical characteristics**

**Architecture**

Number of poles	2 P
Type of pole	2 P
Curve	C

**Main electrical features**

Rated operational voltage Ue	415 V
Frequency	50/60 Hz
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

**Electric current**

Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	10 kA
--	-------

**Electric current / temperature**

Rating current 30°C	100 A
---------------------	-------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	90 mm
Width of installed product	53 mm

**Power**

Total power loss under IN	16.33 W
---------------------------	---------

**Endurance**

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

**Installation, mounting**

Tightening torque	3,5 to 5Nm
-------------------	------------

**Connection**

Connection cross-sect. flexible conductor	50mm <sup>2</sup>
Connection cross-sect. rigid cable	70mm <sup>2</sup>
Type of connection	terminal with tightening compensation system

**Standards**

