



HNB125Z

Moulded Case Circuit Breaker x250 3P 40kA 125A TM

Technical characteristics

Architecture

Number of poles	3 P
-----------------	-----

Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

Power

Total power loss under IN	27.7 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Connection

Connection cross-sect. flexible conductor	35 / 150mm ²
Type of connection	Terminal

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...70 °C
-----------------------	-------------