



HNB250H

## Moulded Case Circuit Breaker X250 3P 40kA 250A TM

### Technical characteristics

#### Architecture

Number of poles	3 P
-----------------	-----

#### Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

#### Power

Total power loss under IN	48 W
---------------------------	------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

#### Connection

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Type of connection	Terminal

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP4X
---------------------	------

#### Use conditions

Operating temperature	-25...70 °C
-----------------------	-------------