



HR440

**EARTH LEAKAGE RELAY 0.03-3A TIME DELAY TORROID 25MM**

**Technical characteristics**

**Main electrical features**

Rated operational voltage  $U_e$  230 V

**Voltage**

Max operating voltage 276 V

Rated impulse withstand voltage 4 kV

**Electric current**

Rated residual operating current 30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A

**Power**

Power consumed 10 VA

**Installation, mounting**

Tightening torque 1Nm

**Connection**

Connection cross-sect. flexible conductor 1 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 1,5 / 4mm<sup>2</sup>

**Standards**

European directive RoHS voluntary compliance

European directive WEEE concerned

**Safety**

Protection index IP IP30

Residual current type A

**Use conditions**

Operating temperature -10...55 °C