



HR440

EARTH LEAKAGE RELAY 0.03-3A TIME DELAY TORROID 25MM

Technical characteristics

Main electrical features

| | |
|--|-------|
| Rated operational voltage U _e | 230 V |
|--|-------|

Voltage

| | |
|-----------------------|-------|
| Max operating voltage | 276 V |
|-----------------------|-------|

| | |
|---------------------------------|------|
| Rated impulse withstand voltage | 4 kV |
|---------------------------------|------|

Electric current

| | |
|----------------------------------|--|
| Rated residual operating current | 30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A |
|----------------------------------|--|

Power

| | |
|----------------|-------|
| Power consumed | 10 VA |
|----------------|-------|

Installation, mounting

| | |
|-------------------|------|
| Tightening torque | 1 Nm |
|-------------------|------|

Connection

| | |
|---|-------------------------|
| Connection cross-sect. flexible conductor | 1 / 2,5 mm ² |
|---|-------------------------|

Standards

| | |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|

Safety

| | |
|-----------------------|---|
| Residual current type | A |
|-----------------------|---|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...55 °C |
|-----------------------|-------------|