



HR441

EARTH LEAKAGE RELAY 0.03-3A TIME DELAY TORROID 35MM

Technical characteristics

Main electrical features

Rated operational voltage U _e	230 V
--	-------

Voltage

Max operating voltage	276 V
-----------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A
----------------------------------	--

Power

Power consumed	10 VA
----------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 2,5mm ²
---	------------------------

Connection cross-sect. rigid cable	1,5 / 4mm ²
------------------------------------	------------------------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
---------------------	------

Residual current type	A
-----------------------	---

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------