



HR441

EARTH LEAKAGE RELAY 0.03-3A TIME DELAY TORROID 35MM

Technical characteristics

Main electrical features

Rated operational voltage Ue 230 V

Voltage

Max operating voltage 276 V

Rated impulse withstand voltage 4 kV

Electric current

Rated residual operating current 30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A

Power

Power consumed 10 VA

Installation, mounting

Tightening torque 1Nm

Connection

Connection cross-sect. flexible conductor 1 / 2,5mm²

Connection cross-sect. rigid cable 1,5 / 4mm²

Standards

European directive RoHs voluntary compliance

European directive WEEE concerned

Safety

Protection index IP IP30

Residual current type A

Use conditions

Operating temperature -10...55 °C