



HR441

## EARTH LEAKAGE RELAY 0.03-3A TIME DELAY TORROID 35MM

### Technical characteristics

#### Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

#### Voltage

Max operating voltage	276 V
Rated impulse withstand voltage	4 kV

#### Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A
----------------------------------	--

#### Power

Power consumed	10 VA
----------------	-------

#### Installation, mounting

Tightening torque	1Nm
-------------------	-----

#### Connection

Connection cross-sect. flexible conductor	1 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 4mm <sup>2</sup>

#### Standards

European directive RoHs	voluntary compliance
European directive WEEE	concerned

#### Safety

Residual current type	A
-----------------------	---

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------