



HR502

EARTH LEAKAGE RELAY 0.3A INSTANT TRIP

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Voltage

Max operating voltage	276 V
-----------------------	-------

Electric current

Rated residual operating current	300 mA
----------------------------------	--------

Power

Power consumed	3 VA
----------------	------

Connection

Connection cross-sect. flexible conductor	1 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 4mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
Residual current type	A

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------