



HR502

EARTH LEAKAGE RELAY 0.3A INSTANT TRIP

Technical Characteristics

Rated operational voltage U _e	230 V
Max operating voltage	276 V
Rated residual operating current	300 mA
Power consumed	3 VA
Number of modules	1
Tightening torque	1,7Nm
Connection cross-sect. flexible conductor	1 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 4mm ²
European directive WEEE	concerned
Protection index IP	IP30
Residual current type	A
Operating temperature	-10...55 °C