



HR510

## EARTH LEAKAGE RELAY 0.03-10A TIME DELAY

### Technical Characteristics

Rated operational voltage Ue	230 V
Max operating voltage	276 V
Rated residual operating current	30 / 100 / 300 / 500 / 1000 / 3000 / 10000 mA
Power consumed	5 VA
Number of modules	3
Tightening torque	1,7Nm
Connection cross-sect. flexible conductor	1 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 4mm <sup>2</sup>
European directive WEEE	concerned
Protection index IP	IP30
Residual current type	A
Operating temperature	-10...55 °C