



HR523

EARTH LEAKAGE RELAY 0.5-30A TIME DELAY 50% LED

Technical characteristics

Main electrical features

Rated operational voltage U_e 230 V

Voltage

Max operating voltage 276 V

Electric current

Rated residual operating current 500 mA / 1 A / 3 A / 5 A / 10 A / 20 A / 30 A

Power

Power consumed 5 VA

Installation, mounting

Tightening torque 1,7Nm

Connection

Connection cross-sect. flexible conductor 1 / 2,5mm²

Connection cross-sect. rigid cable 1,5 / 4mm²

Standards

European directive WEEE concerned

Safety

Protection index IP IP30

Residual current type A

Use conditions

Operating temperature -10...55 °C