



HR523

EARTH LEAKAGE RELAY 0.5-30A TIME DELAY 50% LED

Technical characteristics

Main electrical features

Rated operational voltage U _e	230 V
--	-------

Voltage

Max operating voltage	276 V
-----------------------	-------

Electric current

Rated residual operating current	500 mA / 1 A / 3 A / 5 A / 10 A / 20 A / 30 A
----------------------------------	---

Power

Power consumed	5 VA
----------------	------

Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 2,5mm ²
---	------------------------

Connection cross-sect. rigid cable	1,5 / 4mm ²
------------------------------------	------------------------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Residual current type	A
-----------------------	---

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------