



HR525

## **EARTH LEAKAGE RELAY 0.03-30A TIME DELAY 50% LCD TEST**

### **Technical characteristics**

#### **Main electrical features**

Rated operational voltage Ue	230 V
------------------------------	-------

#### **Voltage**

Max operating voltage	276 V
-----------------------	-------

#### **Electric current**

Rated residual operating current	30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A / 5 A / 10 A / 30 A
----------------------------------	---

#### **Power**

Power consumed	6 VA
----------------	------

#### **Installation, mounting**

Tightening torque	0,5/0,6Nm
-------------------	-----------

#### **Safety**

Residual current type	A
-----------------------	---

#### **Use conditions**

Operating temperature	-10...55 °C
-----------------------	-------------