



HR534

EARTH LEAKAGE RELAY 0.03-30A TIME DELAY 50% LCD TEST 4 WAYS

Technical characteristics

Main electrical features

Rated operational voltage Ue 230 V

Voltage

Max operating voltage 276 V

Electric current

Rated residual operating current 30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A / 5 A / 10 A / 30 A

Power

Power consumed 6 VA

Installation, mounting

Tightening torque 0,5/0,6Nm

Connection

Connection cross-sect. flexible conductor 0,5 / 2mm²

Connection cross-sect. rigid cable 0,5 / 2mm²

Standards

European directive WEEE concerned

Safety

Protection index IP IP30

Residual current type A

Use conditions

Operating temperature -10...55 °C