



HR534

EARTH LEAKAGE RELAY 0.03-30A TIME DELAY 50% LCD TEST 4 WAYS

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Voltage

Max operating voltage	276 V
-----------------------	-------

Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 500 mA / 1 A / 3 A / 5 A / 10 A / 30 A
----------------------------------	--

Power

Power consumed	6 VA
----------------	------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
---------------------	------

Residual current type	A
-----------------------	---

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------