



HR820

RECTANGULAR SECTION TORROID 20X30MM

Technical characteristics

Voltage

Rated impulse withstand voltage	4000 V
---------------------------------	--------

Connection

Connection cross-sect. flexible conductor	1 / 2,5mm ²
Connection cross-sect. rigid cable	1,5 / 4mm ²

Standards

European directive WEEE	not concerned
-------------------------	---------------

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------