



HR821

**RECTANGULAR SECTION TORROID 50X80MM**

**Technical Characteristics**

Rated impulse withstand voltage	4000 V
Maximum connection distance between receiver and transmitter	25m and 50m twisted pair
Tightening torque	1Nm
Connection cross-sect. flexible conductor	1 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 4mm <sup>2</sup>
Can be accessorized	No
European directive WEEE	not concerned
Protection index IP	IP31
Operating temperature	-10...55 °C