



HXA024H

Alarm contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)

Technical characteristics

Architecture

Fixing mode Clipped

Main electrical features

Rated operational voltage U_e 250 V

Type of supply voltage AC/DC

Voltage

Rated impulse withstand voltage 1500 V

Power

Total power loss under IN 3 W

Connection

Type of connection quick connect

Type of contacts 1 NO/NC

Equipment

Number of auxiliary contacts as normally closed contact 1

Number of auxiliary contacts as normally open contact 1

Number of auxiliary contacts as change-over contact 0

Standards

European directive RoHS voluntary compliance

European directive WEEE concerned

Safety

Protection index IP IP4X