



HXA024H

**Alarm contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)**

**Technical characteristics**

**Architecture**

Fixing mode Clipped

**Main electrical features**

Rated operational voltage  $U_e$  250 V

Type of supply voltage AC/DC

**Voltage**

Rated impulse withstand voltage 1500 V

**Power**

Total power loss under IN 3 W

**Connection**

Type of connection quick connect

Type of contacts 1 NO/NC

**Equipment**

Number of auxiliary contacts as normally closed contact 1

Number of auxiliary contacts as normally open contact 1

Number of auxiliary contacts as change-over contact 0

**Standards**

European directive RoHS voluntary compliance