



HXA024H

Alarm contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)

Technical Characteristics

Architecture

Fixing mode	Clipped
-------------	---------

Main electrical features

Rated operational voltage Ue	250 V
Rated current	3 A
Type of supply voltage	AC/DC

Voltage

Rated impulse withstand voltage	1500 V
---------------------------------	--------

Power

Total power loss under IN	3 W
---------------------------	-----

Connection

Type of connection	quick connect
Type of contacts	1 NO/NC

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	1

Standards

European directive RoHS	voluntary compliance
European directive WEEE	concerned

Safety

Protection index IP	IP4X
---------------------	------