



HXA025H

Auxiliary low level 1NO+1NC 125V AC (x160-P160-x250-P250-x630-P630)

Technical Characteristics

Architecture

Fixing mode Clipped

Main electrical features

Rated operational voltage U_e 125 V

Power

Total power loss under IN 3 W

Connection

Type of connection quick connect

Type of contacts 1 NO/NC

Standards

European directive WEEE concerned

Safety

Protection index IP IP4X