



HXA026H



Alarm contact low level 1NO+1NC 125V AC (x160-P160-x250-P250-x630-P630)

Technical characteristics

Architecture

Fixing mode Clipped

Main electrical features

Rated operational voltage U_e 125 V

Voltage

Rated impulse withstand voltage 1500 V

Power

Total power loss under IN 3 W

Equipment

Number of auxiliary contacts as normally closed contact 1

Number of auxiliary contacts as normally open contact 1

Number of auxiliary contacts as change-over contact 0

Standards

European directive RoHS voluntary compliance

European directive WEEE concerned