



HXA026H



**Alarm contact low level 1NO+1NC 125V AC (x160-P160-x250-P250-x630-P630)**

**Technical Characteristics**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Main electrical features**

Rated operational voltage Ue	125 V
------------------------------	-------

Rated current	0.1 A
---------------	-------

Type of supply voltage	AC/DC
------------------------	-------

**Voltage**

Rated impulse withstand voltage	1500 V
---------------------------------	--------

**Power**

Total power loss under IN	3 W
---------------------------	-----

**Connection**

Type of connection	quick connect
--------------------	---------------

Type of contacts	1 NO/NC
------------------	---------

**Equipment**

Number of auxiliary contacts as normally closed contact	0
---	---

Number of auxiliary contacts as normally open contact	0
---	---

Number of auxiliary contacts as change-over contact	1
---	---

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP4X
---------------------	------