



HXB042H

**Motor operator x250 230-240VAC**

**Technical characteristics**

**Main electrical features**

Rated operational voltage $U_e$	220 / 240 V
Frequency	50/60 Hz
Type of supply voltage	AC

**Power**

Total power loss under $I_N$	24 W
------------------------------	------

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------