



JG42BS

Enclosed Non-Auto MCCB 3-Pole, 250A, 25kA

Technical Characteristics

Fixing mode	surface-mounting
Rated current	250 A
Depth of installed product	135 mm
Height of installed product	660 mm
Width of installed product	260 mm
Type of door closing	non keylock
Interlockable	No
Colour	RAL 7035
Material	Steel
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP3X
Protection class	Protection class III