



JG48BM

**Enclosed MCCB 3-Pole 630A, 50kA (Adjustable 252A - 630A)**

**Technical Characteristics**

Fixing mode	surface-mounting
Rated current	630 A
Depth of installed product	153 mm
Height of installed product	1130 mm
Width of installed product	500 mm
Type of door closing	non keylock
Interlockable	No
Colour	RAL 7035
Material	Steel
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP3X
Protection class	Protection class III