



JK108BGSPD

125A 8 Way TPN Board with 4 pole SD & Type II SPD Glazed

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50 Hz

Dimensions

Depth of installed product 132.5 mm

Height of installed product 625 mm

Width of installed product 465 mm

Cover, door

Type of door closing Quarter turn lock

Interlockable Yes

Materials

Colour RAL 7035

RAL colour RAL 7035 - Light grey

Material Steel

Equipment

Can be accessorized Yes

Standards

European directive WEEE concerned

Safety

Protection index IP IP30

Protection class isol.class I

Use conditions

Operating temperature 50...-10 °C