



JK112BDFG

JK112 64 Module Side DIN Rail Box Glazed

Technical characteristics

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rows	4
With lock	Yes
Has neutral terminal block	Yes
Has earthing terminal block	Yes

Capacity

Number of modules	64
-------------------	----

Dimensions

Height	850 mm
Width	465 mm
Depth	132.50 mm
Number of width units	64

Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP3X
Locking type	Key lock, Quarter turn lock