



JK112BGSPD

## 125A 12 Way TPN Board with 4 pole SD & Type II SPD Glazed

### Technical characteristics

#### Architecture

|             |                  |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

#### Main electrical features

|           |       |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

#### Dimensions

|                             |          |
|-----------------------------|----------|
| Depth of installed product  | 132.5 mm |
| Height of installed product | 850 mm   |
| Width of installed product  | 465 mm   |

#### Cover, door

|                      |                   |
|----------------------|-------------------|
| Type of door closing | Quarter turn lock |
| Interlockable        | Yes               |

#### Materials

|            |                       |
|------------|-----------------------|
| Colour     | RAL 7035              |
| RAL colour | RAL 7035 - Light grey |
| Material   | Steel                 |

#### Equipment

|                     |     |
|---------------------|-----|
| Can be accessorized | Yes |
|---------------------|-----|

#### Standards

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

#### Safety

|                     |              |
|---------------------|--------------|
| Protection index IP | IP30         |
| Protection class    | isol.class I |

#### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | 50...-10 °C |
|-----------------------|-------------|