



JK112BGSPD

125A 12 Way TPN Board with 4 pole SD & Type II SPD Glazed

Technical Characteristics

Fixing mode	surface-mounting
Frequency	50 Hz
Rated current	125 A
Depth of installed product	132.5 mm
Height of installed product	850 mm
Width of installed product	465 mm
Number of modules	36
Type of door closing	Quarter turn lock
Interlockable	Yes
Colour	RAL 7035
RAL colour number	7035
Material	Steel
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP30
Protection class	isol.class I
Operating temperature	50...-10 °C