



JK116BDFG

### JK116 80 Module Side DIN Box Glazed

#### Technical characteristics

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rows	5
With lock	Yes
Has neutral terminal block	Yes
Has earthing terminal block	Yes

#### Capacity

Number of modules	80
-------------------	----

#### Dimensions

Height	950 mm
Width	465 mm
Depth	132.50 mm
Number of width units	80

#### Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

#### Materials

Material	Steel
RAL code	7035
Colour	Light grey

#### Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock, Quarter turn lock