



JK118BGSPD

**125A 18 Way TPN Board with 4 pole SD & Type II SPD Glazed**

**Technical characteristics**

**Architecture**

Fixing mode surface-mounting

**Main electrical features**

Frequency 50 Hz

**Dimensions**

Depth of installed product 132.5 mm

Height of installed product 1100 mm

Width of installed product 465 mm

**Cover, door**

Type of door closing Quarter turn lock

Interlockable Yes

**Materials**

Colour RAL 7035

RAL colour RAL 7035 - Light grey

Material Steel

**Equipment**

Can be accessorized Yes

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP30

Protection class isol.class I

**Use conditions**

Operating temperature 50...-10 °C