



JK140MID

## JK Multifunction Meter Pack 125A Pulsed and Modbus MID

### Technical characteristics

#### Architecture

Type of pole	3P+N
Fixing mode	Din-Rail or on a fixing plate

#### Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

#### Dimensions

Depth of installed product	66 mm
Height of installed product	118.5 mm
Width of installed product	70 mm

#### Measurement

Type of measuring instrument	digital
------------------------------	---------

#### Power supply

Supply voltage	230/400 V +/- 15%
----------------	-------------------

#### Materials

Colour	light grey
--------	------------

#### Equipment

Type of display	LCD
-----------------	-----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection class	Protection class III
------------------	----------------------

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------