



JK140MID

## JK Multifunction Meter Pack 125A Pulsed and Modbus MID

### Technical characteristics

#### Architecture

Type of pole	3P+N
--------------	------

#### Electric current

Rated current	125 A
Maximum measuring circuit current	6,000 A

#### Capacity

Number of modules	4
-------------------	---

#### Dimensions

Height	118.50 mm
Width	70 mm
Depth	66 mm

#### Installation, mounting

Mounting on	DIN rail, Mounting plate
-------------	--------------------------

#### Measurement

Measuring system	Measurement transformer
Type of measuring instrument	Digital
Current measurement range	5 - 6,000 A
Frequency measuring range	50 - 50 Hz

#### Power supply

Number of phases for power supply	3
-----------------------------------	---

#### Functions

Accuracy class	1
Tariff type	Multi-tariff
Is calibrated	Yes

#### Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 75 °C

#### Frequency

Frequency	50 - 50 Hz
-----------	------------