



JK140MID

JK Multifunction Meter Pack 125A Pulsed and Modbus MID

Technical characteristics

Architecture

Type of pole	3P+N
--------------	------

Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

Dimensions

Depth of installed product	66 mm
Height of installed product	118.5 mm
Width of installed product	70 mm

Measurement

Type of measuring instrument	digital
------------------------------	---------

Power supply

Supply voltage	230/400 V +/- 15%
----------------	-------------------

Materials

Colour	light grey
--------	------------

Equipment

Type of display	LCD
-----------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	Protection class III
------------------	----------------------

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------