



JK20220BGSD

250A 2+20 Way Hybrid TPN With Switch Disconnecter and Glazed Door

Technical characteristics

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Functions

| | |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection | No |

Capacity

| | |
|-------------------|----|
| Number of modules | 60 |
|-------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

Dimensions

| | |
|--------|-----------|
| Depth | 165.50 mm |
| Height | 1,400 mm |
| Width | 465 mm |

Cover, door

| | |
|---------------------------|-----|
| Interlockable | No |
| Door/cover is transparent | Yes |

Materials

| | |
|----------|------------|
| RAL code | 7035 |
| Colour | Light grey |
| Material | Steel |

Connection

| | |
|-----------------------------|---|
| Number of accessible phases | 3 |
|-----------------------------|---|

Scope of delivery

| | |
|-----------------------------|---|
| Number of RCCB in enclosure | 0 |
|-----------------------------|---|

Safety

| | |
|-------------------------------|-------------------|
| Ingress Protection (IP) class | IP30 |
| Protection class | Isolation class I |