



JK208BDFG

### JK208 80 Module Side DIN Box Glazed

#### Technical characteristics

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Electric current

Rated current	250 A
---------------	-------

##### Equipment

Number of rows	5
With lock	Yes
Has neutral terminal block	Yes
Has earthing terminal block	Yes

##### Capacity

Number of modules	80
-------------------	----

##### Dimensions

Height	950 mm
Width	465 mm
Depth	165.50 mm
Number of width units	80

##### Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

##### Materials

Material	Steel
RAL code	7035
Colour	Light grey

##### Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock, Quarter turn lock