



JK212BDFG

JK212 80 Module Side DIN Box Glazed

Technical characteristics

Architecture

Fixing mode surface-mounting

Dimensions

Depth of installed product 165.5 mm

Height of installed product 1100 mm

Width of installed product 465 mm

Cover, door

Type of door closing Quarter turn lock

Door locking with key

Materials

Colour beige

RAL colour RAL 7035 - Light grey

Material Steel

Equipment

Number of rows 5

Standards

European directive WEEE concerned

Safety

Protection index IP IP3X