



JK216BDFG

## JK216 96 Module Side DIN Box Glazed

### Technical characteristics

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	250 A
---------------	-------

#### Equipment

Number of rows	6
With lock	Yes
Has neutral terminal block	Yes
Has earthing terminal block	Yes

#### Capacity

Number of modules	96
-------------------	----

#### Dimensions

Height	1,250 mm
Width	465 mm
Depth	165.50 mm
Number of width units	96

#### Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

#### Materials

Material	Steel
RAL code	7035
Colour	Light grey

#### Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP3X
Locking type	Key lock, Quarter turn lock