



JK216EG

## JK2 16 Module DIN Rail Box Glazed

### Technical characteristics

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	250 A
---------------	-------

#### Equipment

Number of rows	1
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes

#### Capacity

Number of modules	16
-------------------	----

#### Dimensions

Height	300 mm
Width	465 mm
Depth	165.50 mm
Number of width units	16

#### Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

#### Materials

Material	Steel
RAL code	7035
Colour	Light grey

#### Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC
Locking type	Quarter turn lock, Without lock