

JK224BDFG

**JK224 128 Module Side DIN Box Glazed**

**Technical characteristics**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	250 A
---------------	-------

**Equipment**

Number of rows	8
With lock	Yes
Has neutral terminal block	Yes
Has earthing terminal block	Yes

**Capacity**

Number of modules	128
-------------------	-----

**Dimensions**

Height	1,550 mm
Width	465 mm
Depth	165.50 mm
Number of width units	128

**Cover, door**

Number of cabinet doors	1
Door/cover is transparent	Yes

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Safety**

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP3X
Locking type	Key lock, Quarter turn lock