



JKD1125MID

## 125A Pulsed & ModBus Meter MID Extension Box

### Technical characteristics

#### Architecture

Number of poles	2 P
Type of pole	3P+N
Fixing mode	surface-mounting

#### Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

#### Dimensions

Depth of installed product	132.5 mm
Height of installed product	300 mm
Width of installed product	465 mm

#### Measurement

Type of measuring instrument	digital
------------------------------	---------

#### Power supply

Supply voltage	230/400 V +/- 15%
----------------	-------------------

#### Materials

Colour	light grey
--------	------------

#### Equipment

Type of display	LCD
-----------------	-----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP2XC
Protection class	isol.class I

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------